


DATI TECNICI



Diametri	Limiti	K	S	"B (L<125)"	"B(L=125:200)"	P
M 5	Min.	3,50	-	16,00	-	-0,80
	Max		8,00			
M 6	Min.	4,00	-	18,00	-	-1,00
	Max		10,00			
M 8	Min.	5,30	-	22,00	28,00	-1,25
	Max		13,00			
M 10*	Min.	6,40	-	26,00	32,00	-1,50
	Max		17,00			
M 12*	Min.	7,50	-	30,00	36,00	-1,75
	Max		19,00			
M 14*	Min.	8,80	-	34,00	40,00	-2,00
	Max		22,00			
M 16	Min.	10,00	-	38,00	44,00	-2,00
	Max		24,00			

Diametri	Limiti	K	S	"B (L<125)"	"B(L=125:200)"	P
M 18	Min.	11,50	-	42,00	48,00	-2,50
	Max		27,00			
M 20	Min.	12,50	-	46,00	52,00	-2,50
	Max		30,00			
M 22	Min.	14,00	-	50,00	56,00	2,50
	Max		32,00			
M 24	Min.	15,00	-	54,00	60,00	3,00
	Max		36,00			
M 27	Min.	17,00	-	60,00	66,00	3,00
	Max		40,00			
M 30	Min.	18,70	-	66,00	72,00	3,50
	Max		46,00			